

Now available from [www.M2Cshop.com](http://www.M2Cshop.com)

# HearPlus 317ci

amplified phone for people with severe hearing loss



handset volume amplified by up to 53dB



superior ergonomics



HAC - hearing aid compatible

HearPlus 317ci combines excellent ergonomics with superb visual aids, improved hearing aid compatibility and enhanced sound adjustments for people with severe hearing loss. An excellent amplified phone that is extremely easy to use and understand.



Doro care electronics



volume control



strobe light

# HearPlus 317c

Color: white / dark grey

## Ergonomics

Light weight handset (lb)	0,48
Heavy stable base, weight (lb)	1,89
Easy to place handset	•
Easy grip comfortable handset	•
High contrast keys with low reflective finish	•
Concave keys	•
Easy clean surfaces	•
Low profile front for easy operation	•

## Hearing

Doro Audio +	•
Maximum amplification (dB)	53
Sending level adjustment (dB)	+/-6
Tone adjustment at 250Hz (dB)	6
Tone adjustment at 4KHz (dB)	12
Hearing Aid Compatible	•
Maximum ringer volume (dB SPL)	91
Lowest ringer centre frequency (Hz)	700
Highest ringer centre frequency (Hz)	2000

## Ringer

Monophonic ring tones	9
Ringer volume settings except off	3
Ringer off setting	•
Ringer strobe	•
Vibration alert outlet	•

## Calling/Talking

Speakerphone	•
Extra large, high contrast display	•
Redial memory	5
Pre dialling	•
One touch memories	4
Easy operation slide volume setting	•
Boost mode	•
Call timer	•
Off hook warning lamp	•

## Handset LCD display

Display with zoom function	•
Extra large display with high contrast	•
Display size (inch)	42,5*9,0
Graphical dot matrix	•
Color display	Black on white / White on Black
Lines / Characters	2/21
Backlit display	•
Big display font	•
Clock	•

## Caller ID

Caller ID on hook*	•
Caller ID off hook (call waiting)*	•
Name display from phone book	•
Name display from the network*	•
Date & time stamp - network*	•
Date & time stamp - internal clock	•
Caller ID memory	10

\* Depending on network support and subscription

Doro Audio+ for improved hearing aid compatibility and enhanced sound amplification including loud handset volume with special boost function, receiver tone adjustment, loud ringer with multiple frequency settings, strobe ringer and compliance with HAC standards at preferred levels.



Now available from [www.M2Cshop.com](http://www.M2Cshop.com)

[www.doro.com](http://www.doro.com)