

# AMPLIDECT 350™

## Amplified Cordless Telephone

Now available to purchase from [www.M2Cshop.com](http://www.M2Cshop.com) - Tel: 0208 829 9130



**The AmpliDECT350 was developed specifically to be used with Hearing Aids on the T position:  
The sound quality is incredibly high due to improvements on the telecoil antenna.**

### CALLING

- Hearing Aid Compatible
- Adjustable receiving volume : up to 30dB
- Adjustable receiving tone control (treble, standard, bass)
- Speaker phone
- Phonebook up to 50 numbers (12 characters, 20 digits)
- Redial function for last 10 outgoing calls
- Choice of 7 languages ( English, French, Spanish, Dutch, Italian, German, Polish and Russian)
- 4 direct memories
- P/T dialing mode

### HANDSET LCD DISPLAY

- Navigational menu
- White backlight
- Backlight on keys
- Clock
- Alarm
- Key lock
- Message waiting icon

### CALLER ID \*

- Name & phone number display
- Caller ID also for Call waiting

### RINGER

- 10 melodies
- Adjustable ringing volume (6 positions)
- Special ring option for 10 numbers
- Vibrating ring / flashing LED ring option
- Loud ringer on the base (4 Positions)

### MULTI HANDSET

- 3-way conference with privacy protection
- Up to 4 bases and up to 5 handsets
- Call transfer of external calls (when using several handsets)

### TECHNICAL SPECIFICATIONS

- 3 batteries ni-Mh 1.2V 600mA
- Standby time : 5 days
- Continuous talk time : 6 hours
- GAP compliant: can be paired up to other cordless phones
- Range: up to 80 metres

### OPTIONAL EXTRA

- 2.5mm Headset jack
- Compatible with the CLHooks 1,5,6

To use the CID facility it will be necessary to subscribe to your network provider's CID service  
Items pictured and details are subject to change at the manufacturer's discretion.

GEEMARC  
**CLEAR SOUND™**  
HEAR THE DIFFERENCE

**geemarc™**  
Telecom SA

[www.M2Cshop.com](http://www.M2Cshop.com)

Now available to purchase from [www.M2Cshop.com](http://www.M2Cshop.com) - Tel: 0208 829 9130